thermoscientific

PRODUCT SPECIFICATIONS

Thermo Scientific Niton XL5 Plus XRF Analyzer

Ţ

Small size, big power

Fast, accurate, versatile XRF analysis

When versatility, low limits of detection (LODs) and high sample throughput are critical, industrial businesses rely on the Thermo Scientific[™] Niton[™] XL5 Plus handheld XRF analyzer. Providing customers with solutions designed to meet their most demanding applications, the Niton XL5 Plus maximizes performance and productivity.

Applications

- Verification of metals and alloys in manufacturing operations
- Non-destructive field inspections for positive material identification
- Point-and-shoot sorting at scrap recycling operations
- Measurement of single or multi-layer coat weight and coating thickness in surface treatment control
- Precious metal assay of bullion and jewelry
- Real-time geochemical analysis for mining exploration
- On-site heavy metal screening of polluted soils
- Screening for hazardous substances in consumer goods
- Custom applications on demand

Analytical performance

Designed to return lab quality results, the Niton XL5 Plus' low limits of detection allow operators to scan a broad range of materials for diverse applications. Identify pure metals and alloys, obtain geochemical data, screen for heavy metals or determine plating and coating thickness. From metals to mining, and everything in between, the Niton XL5 Plus is ready to work.

Rapid results

Powered by a 5W x-ray tube, the Niton XL5 Plus generates fast and accurate results. A dynamic current adjustment ensures optimum sensitivity for each measurement - even light elements. Results are displayed in real time, enabling you to make faster decisions. And with a standard system health check designed to verify operating parameters, you'll get to your results even sooner.

Size and weight

Make light work of heavy industrial tasks utilizing the Niton XL5 Plus. Weighing an industry leading 2.8 pounds (1.3 kilograms), the Niton XL5 Plus is the lightest handheld XRF analyzer available for elemental determination and alloy identification.¹ It's small footprint and featherweight design reduce operator fatigue while increasing productivity.

Design

Tight spots are no match for the Niton XL5 Plus. Discover





The Niton XL5 Plus in use, analyzing a tight weld in an oil refinery.

expanded field use with improved compact geometry and ergonomics. Reaching tight welds, corners and joints, are no longer defined as awkward test spots for the Niton XL5 Plus. A rugged graphene window with standard Detector ProGuard protection also reduces risk when measuring sharp items.

Functionality

Vivid new icons and an application interface ease navigation and configuration. Utilize swipe and touchscreen functionality, even with a gloved hand. Optional directional keys provide added usability. A hot swap battery keeps you up and running when it's time to replace a low battery. Micro and macro cameras enable precise sample positioning and collect images for better record keeping. Finally, WiFi accessibility automatically transmits data from your device to PC.



PRODUCT SPECIFICATIONS

Thermo Scientific Niton XL5 Plus XRF Analyzer

Small size, big power

Fast, accurate, versatile XRF analysis

When versatility, low limits of detection (LODs) and high sample throughput are critical, industrial businesses rely on the Thermo Scientific[™] Niton[™] XL5 Plus handheld XRF analyzer. Providing customers with solutions designed to meet their most demanding applications, the Niton XL5 Plus maximizes performance and productivity.

Applications

- Verification of metals and alloys in manufacturing operations
- Non-destructive field inspections for positive material identification
- Point-and-shoot sorting at scrap recycling operations
- Measurement of single or multi-layer coat weight and coating thickness in surface treatment control
- Precious metal assay of bullion and jewelry
- Real-time geochemical analysis for mining exploration
- On-site heavy metal screening of polluted soils
- Screening for hazardous substances in consumer goods
- Custom applications on demand

Analytical performance

Designed to return lab quality results, the Niton XL5 Plus' low limits of detection allow operators to scan a broad range of materials for diverse applications. Identify pure metals and alloys, obtain geochemical data, screen for heavy metals or determine plating and coating thickness. From metals to mining, and everything in between, the Niton XL5 Plus is ready to work.

Rapid results

Powered by a 5W x-ray tube, the Niton XL5 Plus generates fast and accurate results. A dynamic current adjustment ensures optimum sensitivity for each measurement - even light elements. Results are displayed in real time, enabling you to make faster decisions. And with a standard system health check designed to verify operating parameters, you'll get to your results even sooner.

Size and weight

Make light work of heavy industrial tasks utilizing the Niton XL5 Plus. Weighing an industry leading 2.8 pounds (1.3 kilograms), the Niton XL5 Plus is the lightest handheld XRF analyzer available for elemental determination and alloy identification.¹ It's small footprint and featherweight design reduce operator fatigue while increasing productivity.

Design

Tight spots are no match for the Niton XL5 Plus. Discover





The Niton XL5 Plus in use, analyzing a tight weld in an oil refinery.

expanded field use with improved compact geometry and ergonomics. Reaching tight welds, corners and joints, are no longer defined as awkward test spots for the Niton XL5 Plus. A rugged graphene window with standard Detector ProGuard protection also reduces risk when measuring sharp items.

Functionality

Vivid new icons and an application interface ease navigation and configuration. Utilize swipe and touchscreen functionality, even with a gloved hand. Optional directional keys provide added usability. A hot swap battery keeps you up and running when it's time to replace a low battery. Micro and macro cameras enable precise sample positioning and collect images for better record keeping. Finally, WiFi accessibility automatically transmits data from your device to PC.



Veight	2.8 lbs with battery (1.3 kg)	
Dimensions	9.54 x 8.19 x 2.67 in (242.56 x 208.17 x 67.9 mm)	
-Ray Source	X-Ray Tube: Ag anode (6-50kV, 0-500uA, 5W max) Six (6) position filter wheel for enhanced spectral range coverage Dynamically adjustable current for optimal sensitivity on every analysis	
etector	High count rate, high resolution, extra large area silicon drift detector 1µm graphene window, detector ProGuard protection included	
pot Size	Standard: 8mm collimation Optional: 3mm small-spot collimation	
nalytical Range	Mg-U (ultra low light element detection), Na (spectrum based detection)	
Calibration Modes	General Metals, Precious Metals, Coatings, Mining, Soils, Electronic Alloys, Plastics, Industrial Lead in Paint, Spectral Fingerprint, TestAll™	
ibraries	Default alloy libraries based on SAE, AISI, ASTM, AA,DIN, GB standards Users may create, clone and edit libraries	
ystem Check	Automatic health indicator and health check verify system integrity and operating conditions to prevent failure	
P Rating	IP54 (splash and dust proof)	
Operating Environment	Temperature: 0°C to 50°C (external fan recommended when ambient temperature is greater than 33°C) Humidity: 10% to 90% relative humidity non-condensing	
Display	Tilting, color, resistive touchscreen display	
Power	12V lithium-ion battery, or 12V DC, 3A, 3.6W power supply Hot swap functionality keeps analyzer powered during battery replacements	
lacro Camera	Integrated CCD macro camera for capturing overview images of parts and tagging measurement locations	
licro Camera	Integrated CCD micro camera for locating and recording measurement positions	
Global Positioning System	Internal GPS and optional external GPS (via Bluetooth) GPS data included with sample information	
Bluetooth	Supports print functionality, external GPS connectivity and barcode reader	
lemory / Data Storage	512 MB internal system memory / 16 GB industrial grade storage Stores approximately 130,000 readings with spectra (fewer if macro and micro images are saved)	
Data Entry	Touchscreen keyboard User customizable data entry Optional wireless remote barcode reader	
Data Transfer	WiFi, USB-c	
perating System	Linux	
upport Software	NitonConnect PC software	
ecurity	Password-protected user security	
anguages	English, Chinese, Spanish, Portuguese, Russian, Japanese, German, Korean, French, Turkish, Italian	
Standard Accessories	Locking shielded carrying case Two (2) lithium-ion battery packs One (1) 110/220 VAC battery charger/ AC adaptor Check samples Safety lanyard PC connection cable (USB)	
Optional Accessories	Thermo Scientific [™] portable test stand Thermo Scientific [™] mini test stand Thermo Scientific [™] backscatter shield Thermo Scientific [™] hotwork stand off Thermo Scientific [™] soil guard Belt holster	
Compliance	Compliance CE, RoHS, FCC, Industry Canada, Safety to IEC 61010-1:2010	
icensing / Registration	Varies by region. Contact your local distributor.	

1. The Thermo ScientificTM NitonTM XL5 XRF Plus analyzer weighs 2.8lbs (1.3 kg). The Niton XL5 Plus is the smallest and lightest handheld XRF analyzer leveraging x-ray tube technology.

Learn more at thermofisher.com/XL5Plus

Americas	Europe, Middle East, Africa	India	Asia Pacific
Boston, USA	Munich, Germany	Mumbai, India	New Territories, Hong Kong
+1.978.670.7460	+49.89.3681380	+91.226.6803000	+852.2885.4613
niton@thermofisher.com	niton.eur@thermofisher.com	ininfo@thermofisher.com	niton.asia@thermofisher.com



© 2020 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. 0820